



Marathon Electric Mfg. Corp. Type MAGNAPLUS[®] Generator Add-On PMG Excitation Support Systems Specifications

Capacity: 840 VA
Duty: Continuous
Volts: 240/200
Power Factor: 1.0
Phase: One
Frequency (Hz): 300/250
RPM: 1800/1500
Full Load Amps: 3.5
Stator Resistance: 2.1 Ohms
Number of Field Poles: 20
Insulation Class: F
Rise by Resistance: 105°C
Maximum Ambient Temperature: 40°C